



BDBMCS2N2, 2-Pole Flex Rated Power Distribution Block

By Burndy
Catalog # [BDBMCS2N2](#)



POWER DISTRIBUTION BLOCKS.

General

Catalog Number	BDBMCS2N2
Connector Type	Power Distribution Block
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSIPOLE™
UPC	781810676042
UPC 12 Digit	7818106760422

- CU C Str-Run
- AL C Str-Tap
- CU C Str-Tap

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor Type	<ul style="list-style-type: none">• AL C Str-Run
----------------	--

Certifications And Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	384

Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50059696](#)
- [Specifications - BDBMCS2N2](#)