




BDBMCS5M1FSKIT, Power Distribution Block Finger Safe Kit

By Burndy
Catalog # BDBMCS5M1FSKIT



FINGER-SAFE KIT.

Features

- AL9CU dual rated for use with copper and aluminum conductors
- Range taking designs accommodate wire sizes up to 535 DLO and can support 1 or 2 run conductors and up to 12 taps for secondary circuits
- Allow for panel mounting, medium and large sizes also allow for DIN rail mounting
- Finger-Safe style are provided with translucent polycarbonate top covers and end plates permitting easy visual inspection, provide IEC 605219 IP-20 Rating
- Base and side barriers of glass-reinforced nylon 6/6 for extra durability and excellent insulating properties
- UL94 flammability rating of VO

General

Connector Type	Power Distribution Block
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	VERSIPOLE™
UPC	621945457539
UPC 12 Digit	6219454575399

Electrical Ratings

Rating - Minimum Voltage 600

Certifications And Compliance

Certification - CSA Approved No
Certification - cULus Yes
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 20
Minimum Pack Quantity 1
Pallet Quantity 4800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50065165](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BDBMCS5M1FSKIT-SPEC-EN | REV 5/2024