

# BDBMHC222/02, 2-Pole Power Distribution Block

By Burndy  
Catalog # BDBMHC222/02



POWER DISTRIBUTION BLOCKS.

## General

Catalog Number	BDBMHC222/02
Insulation	Y
Material	Aluminum
Number Of Poles	2
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSIPOLE™
UPC	781810645918
UPC 12 Digit	7818106459188

## Dimensions

Dimension - Height inch	3.25 in
Dimension - Height mm	82.6 mm
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	3.57 in
Dimension - Width mm	91 mm

## Electrical Ratings

Amperage Rating	350 A
Rating - Minimum Voltage	600

## Conductor Related

Conductor - AL Str Run	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Tap	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Tap Range	12-2/0
Conductor - Copper Str Run	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0

Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Tap Range	14-2/0
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	9
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_VERSIPOLE\\_Medium\\_Lineart](#)
- [Sales Drawings - 50018989](#)
- [Specifications - BURNDY\\_BDBMHC22202\\_Specsheet](#)
- [Specifications - BDBMHC222/02](#)