



BDBMHC262/01, 1-Pole Power Distribution Block

By Burndy
Catalog # BDBMHC262/01



POWER DISTRIBUTION BLOCKS, 1 POLE 600V AL9CU, RUN (2)
#14-2/0 AWG TAP:(6) #14-#2.

General

Catalog Number	BDBMHC262/01
Construction Material - Main	HIGHLY CONDUCTIVE TIN-PLATED ALUMINUM
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Poles	1
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	POWER DISTRIBUTION BLOCK
UPC	781810646021
UPC 12 Digit	7818106460211

Dimensions

Dimension - Height inch	3.25 in
Dimension - Height mm	82.6 mm
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	1.85 in
Dimension - Width mm	47 mm
Dimensions	5 in x 1.85 in x 3.25 in
Height	3.25 in
Length	5 in
Width	1.85 in

Electrical Ratings

Amperage Rating	350 A
Rating - Minimum Voltage	600
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Run	12;10;8;6;4;3;2;1;1/0;2/0
------------------------	---------------------------

Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Tap	12;10;8;6;4;3;2
Conductor - AL Str Tap Range	12-2
Conductor - Copper Str Run	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2
Conductor - Copper Str Tap Range	14-2
Conductor Type	<ul style="list-style-type: none">AL C Str-RunCU C Str-RunAL C Str-TapCU C Str-Tap

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	18
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_VERSIPOLE_Medium_Lineart](#)
- [Sales Drawings - 50018989](#)
- [Specifications - BURNDY_BDBMHC26201_Specsheet](#)
- [Specifications - BDBMHC262/01](#)