



BDBMHC262/03, 3-Pole Power Distribution Block

By Burndy

Catalog # [BDBMHC262/03](#)

Terminal block covers, AWG 14 - 2/O (Run), AWG 14 - 2 (Tap), Power Distribution Block, Amp rating:350



General

Application	Industrial control feeder, HVAC system and wire ways
Catalog Number	BDBMHC262/03
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Number Of Poles	3
Plated	Y
Plating Type	Tin
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810646045
UPC 12 Digit	7818106460455

Dimensions

Dimension - Height inch	3.25 in
Dimension - L Length Overall mm	127 mm
Dimension - Length Overall inch	5.00 in
Dimension - Width inch	5.28 in
Dimension - Width mm	134 mm

Electrical Ratings

Amperage Rating	350 A
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Run	12;10;8;6;4;3;2;1;1/0;2/0
Conductor - AL Str Run Range	12-2/0
Conductor - AL Str Tap	12;10;8;6;4;3;2
Conductor - AL Str Tap Range	12-2
Conductor - Copper Str Run	14;12;10;9;8;7;6;5;4;3;2;1;1/0;2/0
Conductor - Copper Str Run Range	14-2/0
Conductor - Copper Str Tap	14;12;10;9;8;7;6;5;4;3;2
Conductor - Copper Str Tap Range	14-2
Conductor Type	AL C Str-Run CU C Str-Run AL C Str-Tap CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_VERSIPOLE_Medium_Lineart](#)
[Sales Drawings - 50018989](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-BDBMHC26203-SPEC-EN | REV 6/2024