

# BDBMHCCOVER, Power Distribution Block Cover

By Burndy  
Catalog # [BDBMHCCOVER](#)



POWER DISTRIBUTION BLOCKS.

## General

Catalog Number	BDBMHCCOVER
Insulation	Y
Material	Polycarbonate
Plated	Y
Plating Type	Unplated
Temperature Rating	194
Trade Name	VERSIPOLE™
UPC	781810646137
UPC 12 Digit	7818106461377

- CU C Str-Run
- AL C Str-Tap
- CU C Str-Tap

## Dimensions

Dimension - Height inch	0.65 in
Dimension - Height mm	16.5 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.37 in
Dimension - Width inch	1.75 in
Dimension - Width mm	44 mm

## Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

## Conductor Related

Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> </ul>
----------------	--

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	200
Minimum Pack Quantity	1

## Product Assets

- [3D Models - BDBMHCCOVER\\_MODEL-IGES](#)
- [3D Models - BDBMHCCOVER\\_MODEL-PDF](#)
- [3D Models - BDBMHCCOVER\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50021140](#)
- [Specifications - BDBMHCCOVER](#)