

## BDBSCS1C3, 3-Pole Flex Rated Power Distribution Block

By Burndy  
Catalog # BDBSCS1C3

Distribution block, Three pole Open Style 14-2/0 AWG (Run), 14-4 AWG (Tap).

### Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

### General

Catalog Number	BDBSCS1C3
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676295
UPC 12 Digit	7818106762955

### Dimensions

Dimension - Height mm	0 mm
-----------------------	------

### Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V



### Conductor Related

Conductor Type	<ul style="list-style-type: none"><li>• AL C Str-Run</li><li>• CU C Str-Run</li><li>• AL C Str-Tap</li><li>• CU C Str-Tap</li></ul>
----------------	---

### Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	832

### Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50059697](#)  
[Specifications - BDBSCS1C3](#)