

BDBSCS1P2, 2-Pole Flex Rated Power Distribution Block

By Burndy
Catalog # BDBSCS1P2

Distribution block, Two pole Open Style 14-2/0 AWG (Run), 14-2/0 (Tap).



Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

General

Catalog Number	BDBSCS1P2
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676158
UPC 12 Digit	7818106761588

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor Type	<ul style="list-style-type: none">AL C Str-RunCU C Str-RunAL C Str-TapCU C Str-Tap
----------------	---

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	832

Product Assets

[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50059697](#)
[Specifications - BDBSCS1P2](#)