

## BDBSCS1P3, 3-Pole Flex Rated Power Distribution Block

By Burndy  
Catalog # BDBSCS1P3

Distribution block, Three pole Open Style 14-2/0 AWG (Run), 14-2/0 (Tap).



### Application

VERSI-POLE Power Distribution Blocks are designed to provide modular solutions to power distribution applications.

### General

Catalog Number	BDBSCS1P3
Connector Type	Power Distribution Block
EU RoHS Indicator	Yes
Insulation	Y
Material	Aluminum
Plated	Y
Plating Type	Tin
Sub Brand	VERSIPOLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810676332
UPC 12 Digit	7818106763322

### Dimensions

Dimension - Height mm	0 mm
-----------------------	------

### Electrical Ratings

Rating - Minimum Voltage	600
Voltage - Maximum	600 V

### Conductor Related

Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>
----------------	--

### Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance	CM
Status	

### Logistics

Carton Quantity	4
Minimum Pack Quantity	1
Pallet Quantity	832

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50059697](#)
- [Specifications - BDBSCS1P3](#)