

# BDBSHCCOVER, Power Distribution Block Cover

By Burndy  
Catalog # [BDBSHCCOVER](#)



Plycarbonate Safety Cover, Power Distribution Blocks.

## Application

Industrial control feeder, HVAC system and wire ways

## General

Catalog Number	BDBSHCCOVER
EU RoHS Indicator	Yes
Insulation	Y
Material	Polycarbonate
Plated	Y
Plating Type	Unplated
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810646144
UPC 12 Digit	7818106461444

## Dimensions

Dimension - Height inch	0.63 in
Dimension - Height mm	16 mm
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.45 in
Dimension - Width inch	0.97 in
Dimension - Width mm	25 mm

## Electrical Ratings

Rating - Minimum Voltage 600

## Conductor Related

Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Run</li> <li>• CU C Str-Run</li> <li>• AL C Str-Tap</li> <li>• CU C Str-Tap</li> </ul>
----------------	--

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	200
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50021140](#)
- [Specifications - BDBSHCCOVER](#)