

BDBSHCCOVER, Power Distribution Block Cover

By Burndy
Catalog # [BDBSHCCOVER](#)



Polycarbonate Safety Cover, Power Distribution Blocks.

Application

Industrial control feeder, HVAC system and wire ways

General

Catalog Number	BDBSHCCOVER
EU RoHS Indicator	Yes
Insulation	Y
Material	Polycarbonate
Plated	Y
Plating Type	Unplated
Sub Brand	VERSI-POLE
Temperature Rating	194
Trade Name	VERSIPOLE™
Type	BDB
UPC	781810646144
UPC 12 Digit	7818106461444

Dimensions

Dimension - Height inch	0.63 in
Dimension - Height mm	16 mm
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.45 in
Dimension - Width inch	0.97 in
Dimension - Width mm	25 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap
----------------	--

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Certified Listed	TAA Compliant (All status valid till December 2024)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50021140](#)
- [Specifications - BDBSHCCOVER](#)