



BDTIBB, BONDIT Wall Mount Intersystem Bonding Connector, #14-#2 AWG

By Burndy
Catalog # [BDTIBB](#)



BONDIT® Wall Mount, #14 - #2 AWG, 4.01 in L, .71 in W

Application

Used to tying all of the system grounds together in one location

General

EU RoHS Indicator	Under Review
Sub Brand	BONDIT
Trade Name	BONDIT®
Type	BDT
UPC	781810504017
UPC 12 Digit	7818105040177

Dimensions

Dimension - Height inch	0.91 in
-------------------------	---------

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	3780

Product Assets

- [3D Models - BDTIBB_MODEL-PDF](#)
- [3D Models - BDTIBB_MODEL-STEP](#)
- [3D Models - BDTIBB_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BDT_LineArt](#)
- [Sales Drawings - 30003958](#)
- [Sell Sheets - BONDIT® Wall Mounted Intersystem Bonding Connectors](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BDTIBB-SPEC-EN | REV 5/2024