



BE12G60TN Flexible Copper Braid

By Burndy
Catalog # BE12G60TN

Tin Plated Ferrules.



General

Catalog Number	BE12G60TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Plating Type	Tin plated
UPC	781810466650
UPC 12 Digit	7818104666500

Dimensions

Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12 in
Dimension - Pad Width inch Length	1.25 in 12 in
Thickness	0.25 in

Certifications And Compliance

Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50089198](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BE12G60TN-SPEC-EN | REV 6/2024