



## BE12T78 Flexible Copper Braid

By Burndy  
Catalog # [BE12T78](#)

Flexible Copper Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number           BE12T78  
Connector Type            Braid

Material	Copper
UPC	781810675120
UPC 12 Digit	7818106751200

### Dimensions

Length	12 in
--------	-------

### Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	UI
Status	

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - BE12T78](#)