



BE13G154TN Flexible Copper Braid

By Burndy

Catalog # [BE13G154TN](#)

Tinned copper flexible braid 13"x1.5"x0.17".



General

Catalog Number	BE13G154TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810426340
UPC 12 Digit	7818104263400

Dimensions

Dimension - L Length Overall mm	330 mm
Dimension - Length Overall inch	13.00 in
Dimension - Width inch	1.5
Dimension - Width mm	38 mm
Length	13 in

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50066428](#)
- [Specifications - BE13G154TN](#)