



BE13NTN Flexible Copper Braid

By Burndy
Catalog # [BE13NTN](#)

Tinned copper flexible braid 13"x1.5"x0.17".



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	1
UPC	621945439764
UPC 12 Digit	6219454397644

Dimensions

Dimension - L Length Overall mm	330
Dimension - Length Overall inch	13
Dimension - Width inch	1.5
Dimension - Width mm	38 mm
Length	13 in

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	10
Pallet Quantity	900

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10036839](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BE13NTN-SPEC-EN | REV 1/2024