



BE14G125TN Flexible Copper Braid

By Burndy
Catalog # [BE14G125TN](#)

Tin Plated Ferrules.



General

Catalog Number	BE14G125TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810161883
UPC 12 Digit	7818101618833

Dimensions

Dimension - L Length Overall mm	356 mm
Dimension - Length Overall inch	14.00 in
Length	14 in

Electrical Ratings

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SC211222-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BE14G125TN-SPEC-EN | REV 6/2024