

BE18D63TNCG1 Flexible Copper Braid

By Burndy
Catalog # [BE18D63TNCG1](#)

Tinned copper flexible braid 18.2"x1.5"x0.17".



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BE18D63TNCG1
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810420980
UPC 12 Digit	7818104209800

Dimensions

Dimension - L Length Overall mm	462 mm
Dimension - Length Overall inch	18.20 in

Dimension - Width inch	1.5
Dimension - Width mm	38 mm
Length	18.63 in
Weight	0.87 lb

Electrical Ratings

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	6
Minimum Pack Quantity	1
Pallet Quantity	576

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BE18D63TNCG1](#)