



## BE18G160TN Tin Plated Copper Braid

By Burndy  
Catalog # [BE18G160TN](#)

Tin Plated Copper Braid.



### General

Catalog Number	BE18G160TN
Connector Type	Braid
Insulation	N
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810456750
UPC 12 Digit	7818104567500

### Dimensions

Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Length	18 in

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [3D Models - BE18G160TN\\_MODEL-STEP](#)
- [3D Models - BE18G160TN\\_MODEL-IGES](#)
- [3D Models - BE18G160TN\\_MODEL-PDF](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10086281](#)
- [Specifications - BE18G160TN](#)