



BE18G218TN Flexible Copper Braid

By Burndy

Catalog # [BE18G218TN](#)

Tin Plated Ferrules.



General

Catalog Number	BE18G218TN
Connector Type	Braid
Material	Copper
UPC	781810665794
UPC 12 Digit	7818106657944

Dimensions

Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Length	18 in

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50038852](#)
- [Specifications - BE18G218TN](#)