

## BE18NW Flexible Copper Braid

By Burndy  
Catalog # BE18NW

Tinned copper flexible braid 18"x1.5"x0.17".



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BE18NW
Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	1
UPC	621945459793
UPC 12 Digit	6219454597933

### Dimensions

Dimension - L Length Overall mm	457
---------------------------------	-----

Dimension - Length Overall inch	18
Dimension - Width inch	1.5
Dimension - Width mm	38 mm
Length	18 in

### Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10036839](#)  
[Specifications - BE18NW](#)