



BE18T12TN Flexible Copper Braid

By Burndy

Catalog # [BE18T12TN](#)

Tin Plated Ferrules.



General

Catalog Number	BE18T12TN
Connector Type	Braid
Material	Copper
UPC	621945435193
UPC 12 Digit	6219454351933

Dimensions

Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18 in
Length	18 in
Weight	1.684 lb

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	2400

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50053103](#)
- [Specifications - BE18T12TN](#)