



## BE18T38G219TN Flexible Copper Braid

By Burndy  
Catalog # BE18T38G219TN

Tin Plated Ferrules.

### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BE18T38G219TN
Connector Type	Braid
Material	Copper
UPC	621945460027
UPC 12 Digit	6219454600277

### Dimensions

Dimension - L Length Overall	457 mm
mm	



Dimension - Length Overall	18 in
inch	
Length	18 in
Weight	2.614 lb

### Certifications And Compliance

Certification - CSA Approved	Yes
Certification - UL Listed Direct	No
Burial	
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	975

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50066986](#)  
[Specifications - BE18T38G219TN](#)