



BE24G113 Flexible Copper Braid

By Burndy

Catalog # [BE24G113](#)

Flexible copper braid 610"x1.5"x0.17".



General

Catalog Number	BE24G113
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810058275
UPC 12 Digit	7818100582755

Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - Width inch	1.5
Dimension - Width mm	38 mm
Length	24 in

Electrical Ratings

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 10023092](#)
- [Specifications - BE24G113](#)



A Hubbell brand