

BE24G114 Flexible Copper Braid

By Burndy
Catalog # [BE24G114](#)

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BE24G114
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810058282
UPC 12 Digit	7818100582822

Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24 in

Length 24 in

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - BE24G114_MODEL-PDF](#)
[3D Models - BE24G114_MODEL-STEP](#)
[3D Models - BE24G114_MODEL-IGES](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10092244](#)
[Specifications - BE24G114](#)