

BE24G194TN Flexible Copper Braid

By Burndy

Catalog # [BE24G194TN](#)

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BE24G194TN
Connector Type	Braid
Material	Copper
UPC	781810566459
UPC 12 Digit	7818105664599

Dimensions

Dimension - L Length Overall	610 mm
mm	

Dimension - Length Overall	24 in
inch	

Length	24 in
--------	-------

Electrical Ratings

Rating - Indoor Amperage	340 A
--------------------------	-------

Rating - Outdoor Amperage	405 A
---------------------------	-------

Certifications And Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
---------------------	----

Certification - UL Recognized	No
-------------------------------	----

Certification - cULus	No
-----------------------	----

Standards - RoHS Compliance	CM
-----------------------------	----

Status	
--------	--

UL Listed	Yes
-----------	-----

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Sales Drawings - 50009664](#)

[Specifications - BE24G194TN](#)