



BE24N2U BE Type Braid, 24" Undrilled

By Burndy
Catalog # [BE24N2U](#)

Tinned Copper Braid, Undrilled, Length:24 in,Ampere Rating-
340 INDOOR, 405 OUTDOOR.



General

UPC 621945485129

Dimensions

Length 24 in

Certifications and Compliance

Certification - CSA Approved Yes

Logistics

Carton Quantity 5
Minimum Pack Quantity 1
Pallet Quantity 450

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50078955](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BE24N2U-SPEC-EN | REV 1/2024