

BE32D50G169TN Flexible Copper Braid

By Burndy

Catalog # [BE32D50G169TN](#)

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BE32D50G169TN
Connector Type	Braid
Material	Copper
UPC	781810511992
UPC 12 Digit	7818105119922

Dimensions

Dimension - L Length Overall	825 mm
mm	

Dimension - Length Overall	32.50 in
inch	
Length	32.5 in

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - BE32D50G169TN_MODEL-IGES](#)
- [3D Models - BE32D50G169TN_MODEL-PDF](#)
- [3D Models - BE32D50G169TN_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30010218](#)
- [Specifications - BE32D50G169TN](#)