



## BE32N Flexible Copper Braid

By Burndy  
Catalog # [BE32N](#)

Flexible Copper Braid.



### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810329382
UPC 12 Digit	7818103293822

### Dimensions

Dimension - L Length Overall mm	813 mm
Dimension - Length Overall inch	32.00 in
Length	32 in

### Electrical Ratings

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 10036839](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-BE32N-SPEC-EN | REV 1/2024