

BE36 Flexible Copper Braid

By Burndy
Catalog # BE36

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

| | |
|---------------------------------------|---------------|
| Catalog Number | BE36 |
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 1 |
| Plated | N |
| UPC | 781810206522 |
| UPC 12 Digit | 7818102065222 |

Dimensions

| | |
|------------------------------|--------|
| Dimension - L Length Overall | 914 mm |
| mm | |

| | |
|----------------------------|----------|
| Dimension - Length Overall | 36.00 in |
| inch | |
| Length | 36 in |

Electrical Ratings

| | |
|---------------------------|-------|
| Rating - Indoor Amperage | 340 A |
| Rating - Outdoor Amperage | 405 A |

Certifications And Compliance

| | |
|---|-------|
| Certification - CSA Approved | Yes |
| Certification - UL Listed Direct Burial | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Carton Quantity | 10 |
| Minimum Pack Quantity | 1 |
| Pallet Quantity | 300 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30019447](#)
[Specifications - BE36](#)