

BEF10G1TN Flexible Copper Braid

By Burndy

Catalog # BEF10G1TN

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BEF10G1TN
Connector Type	Braid
Material	Copper
UPC	781810499917
UPC 12 Digit	7818104999177

Dimensions

Dimension - L Length Overall	254 mm
mm	
Dimension - Length Overall	10 in
inch	
Length	10 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Minimum Pack Quantity	1200
-----------------------	------

Product Assets

[3D Models - BEF10G1TN_MODEL-IGES](#)
[3D Models - BEF10G1TN_MODEL-PDF](#)
[3D Models - BEF10G1TN_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30000290](#)
[Specifications - BEF10G1TN](#)