



BF12N Flexible Copper Braid

By Burndy
Catalog # [BF12N](#)

Cu Flexible Braid Jumper, 2 NEMA Holes 2 Ferrules, 1.75" Spacing, 12.00" L, .56" Hole Dia., Amp Rating: 360(Indoor) 430(Outdoor).



General

Catalog Number	BF12N
Connector Type	Braid
Construction Material - Main	Copper
EU RoHS Indicator	Contact Manufacturer
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Sub Brand	Braid
Type	B
UPC	781810004883
UPC 12 Digit	7818100048833

Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.19 in
Length	12 in

Electrical Ratings

Rating - Indoor Amperage	360
Rating - Outdoor Amperage	430

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BD_Lineart](#)
[Sales Drawings - SE..210201-01](#)
[Specifications - BF12N](#)