

BF22D25G27 Flexible Copper Braid

By Burndy

Catalog # BF22D25G27

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	BF22D25G27
Connector Type	Braid
Material	Copper
UPC	781810657904
UPC 12 Digit	7818106579044

Dimensions

Dimension - L Length Overall	565 mm
mm	

Dimension - Length Overall	22.25 in
inch	
Length	22.25 in

Electrical Ratings

Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	403 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	1260

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50032827](#)
[Specifications - BF22D25G27](#)