



BF24N Flexible Cu Braid Jumper, 24" L, Amp Rating: 360(Indoor), 430(Outdoor)

By Burndy
Catalog # BF24N



Flexible Cu Braid Jumper, 24" L, Amp Rating:
360(Indoor),430(Outdoor).

Application

For Outdoor And Indoor Use

General

Catalog Number	BF24N
Connector Type	Braid
EU RoHS Indicator	Yes
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Sub Brand	BRAID JUMPER
Type	B, Flexible
UPC	781810005170
UPC 12 Digit	7818100051700

Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.19 in
Length	24 in

Electrical Ratings

Rating - Indoor Amperage	360 A
Rating - Outdoor Amperage	430 A

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_BD_Lineart](#)
[Sales Drawings - SE..210201-01](#)
[Specifications - BF24N](#)