

## BF26N Flexible Copper Braid

By Burndy  
Catalog # [BF26N](#)

Flexible Copper Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

|                                       |               |
|---------------------------------------|---------------|
| Catalog Number                        | BF26N         |
| Connector Type                        | Braid         |
| Material                              | Copper        |
| Material - Ferrules                   | Y             |
| Physical Attribute - Number of Braids | 1             |
| Plated                                | Y             |
| UPC                                   | 781810201732  |
| UPC 12 Digit                          | 7818102017322 |

### Dimensions

|                              |          |
|------------------------------|----------|
| Dimension - L Length Overall | 660 mm   |
| mm                           |          |
| Dimension - Length Overall   | 26.00 in |
| inch                         |          |
| Length                       | 26 in    |

### Certifications And Compliance

|                                         |       |
|-----------------------------------------|-------|
| Certification - CSA Approved            | Yes   |
| Certification - ETL                     | No    |
| Certification - UL Listed Direct Burial | No    |
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | EX    |
| UL Listed                               | Yes   |

### Logistics

|                       |      |
|-----------------------|------|
| Carton Quantity       | 25   |
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 2250 |

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Specifications - BF26N](#)