



BF33D50G87TN Flexible Copper Braid

By Burndy
Catalog # [BF33D50G87TN](#)

Tin Plated Ferrules.



General

Catalog Number	BF33D50G87TN
Connector Type	Braid
Material	Copper
UPC	781810537909
UPC 12 Digit	7818105379099

Dimensions

Dimension - D inch	1.50 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	851 mm
Dimension - Length Overall inch	33.50 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch	1.19 in
Length	33.5 in

Electrical Ratings

Rating - Indoor Amperage	360 A
Rating - Outdoor Amperage	430 A

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_2F_LineArt](#)
[Sales Drawings - 30021187](#)
[Specifications - BF33D50G87TN](#)