



BF6T716 Flexible Copper Braid

By Burndy
Catalog # BF6T716

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

General

Catalog Number	BF6T716
Connector Type	Braid
Material	Copper
UPC	621945431577
UPC 12 Digit	6219454315777

Dimensions

Dimension - D inch	1.50 in
Dimension - Hole Size inch	0.50 in
Dimension - L Length Overall mm	152 mm

Dimension - Length Overall inch	6 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch	1.19 in
Length	6 in

Electrical Ratings

Rating - Indoor Amperage	360 A
Rating - Outdoor Amperage	430 A

Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	1480

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50053106](#)
- [Specifications - BF6T716](#)