



## BG10D25N Flexible Copper Braid

By Burndy  
Catalog # [BG10D25N](#)

Flexible Copper Braid.



### General

Catalog Number	BG10D25N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810206553
UPC 12 Digit	7818102065533

### Dimensions

Dimension - D inch	3 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	260 mm
Dimension - Length Overall inch	10.25 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.50 in
Length	10.25 in

### Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 10077022](#)



A proud member of the Hubbell Family.