



BG1200N Flexible Copper Braid

By Burndy
Catalog # [BG1200N](#)

Flexible Copper Braid.



General

Catalog Number	BG1200N
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	N
UPC	781810470312
UPC 12 Digit	7818104703122

Dimensions

Dimension - D inch	3 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	30480 mm
Dimension - Length Overall inch	1200 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.50 in
Length	1200 in

Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

Certifications And Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10077022](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BG1200N-SPEC-EN | REV 6/2024