

BG12G122 Braid Kit

By Burndy

Catalog # [BG12G122](#)

Copper braid 12.00"x1.63"x0.25".



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BG12G122
Connector Type	Braid
Material	Copper
UPC	621945449787
UPC 12 Digit	6219454497877

Dimensions

Dimension - L Length Overall	305 mm
mm	
Dimension - Length Overall	12 in
inch	
Dimension - Width inch	1.63 in
Length	12 in
Weight	2.022 lb

Certifications And Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	1680

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50060538](#)
[Specifications - BG12G122](#)