

## BG12T12 Flexible Copper Braid

By Burndy  
Catalog # [BG12T12](#)

Flexible Copper Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BG12T12
Connector Type	Braid
Material	Copper
UPC	781810675212
UPC 12 Digit	7818106752122

### Dimensions

Dimension - D inch	1.50 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	305 mm

Dimension - Length Overall inch	12 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch	1.50 in
Length	12 in

### Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

### Certifications And Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	1050

### Product Assets

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50047630](#)  
[Specifications - BG12T12](#)