



BG12T716 Flexible Copper Braid

By Burndy
Catalog # [BG12T716](#)

Flexible Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	BG12T716
Connector Type	Braid
Material	Copper
UPC	781810675199

UPC 12 Digit 7818106751999

Dimensions

Length 12 in

Certifications And Compliance

Certification - CSA Approved Yes
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 25
Minimum Pack Quantity 1
Pallet Quantity 4200

Product Assets

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BG12T716](#)