



BG18G36W Flexible Copper Braid

By Burndy

Catalog # [BG18G36W](#)

Tin Plated Ferrules.



General

Catalog Number	BG18G36W
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810059401
UPC 12 Digit	7818100594011

Dimensions

Dimension - D inch	3.12 in
Dimension - Hole Size inch	0.62 in
Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.50 in
Length	18 in

Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50025657](#)
[Specifications - BG18G36W](#)