

## BG19N Flexible Copper Braid

By Burndy  
Catalog # BG19N

Flexible Copper Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	BG19N
Connector Type	Braid
Material	Copper
UPC	781810550953
UPC 12 Digit	7818105509533

### Dimensions

Dimension - L Length Overall	483 mm
mm	

Dimension - Length Overall	19.00 in
inch	
Length	19 in

### Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10077022](#)  
[Specifications - BG19N](#)