

## BG36N Flexible Copper Braid

By Burndy  
Catalog # BG36N



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

|                                       |               |
|---------------------------------------|---------------|
| Catalog Number                        | BG36N         |
| Connector Type                        | Braid         |
| Material                              | Copper        |
| Material - Ferrules                   | Y             |
| Physical Attribute - Number of Braids | 1             |
| Plated                                | Y             |
| UPC                                   | 781810130803  |
| UPC 12 Digit                          | 7818101308033 |

### Dimensions

|                              |          |
|------------------------------|----------|
| Dimension - L Length Overall | 914 mm   |
| mm                           |          |
| Dimension - Length Overall   | 36.00 in |
| inch                         |          |
| Length                       | 36 in    |

### Electrical Ratings

|                           |       |
|---------------------------|-------|
| Rating - Indoor Amperage  | 415 A |
| Rating - Outdoor Amperage | 495 A |

### Certifications And Compliance

|                                |       |
|--------------------------------|-------|
| Certification - CSA Approved   | No    |
| Certification - ETL            | No    |
| Certification - UL Recognized  | No    |
| Certification - cULus          | No    |
| Industry Standard(s)           | UL467 |
| Standards - Industry Standards | UL467 |
| Met                            |       |
| Standards - RoHS Compliance    | EX    |
| Status                         |       |
| UL Listed                      | Yes   |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10077022](#)  
[Specifications - BG36N](#)