



BG48N Flexible Copper Braid

By Burndy
Catalog # [BG48N](#)

Flexible Copper Braid.



General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810051221
UPC 12 Digit	7818100512211

Dimensions

Dimension - L Length Overall mm	1219 mm
Dimension - Length Overall inch	48.00 in
Length	48 in

Electrical Ratings

Rating - Indoor Amperage	415
Rating - Outdoor Amperage	495

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SE..210201-01](#)



A proud member of the Hubbell Family.