



## BG96NTN Flexible Copper Braid

By Burndy  
Catalog # [BG96NTN](#)

Tin Plated Ferrules.



### General

Catalog Number	BG96NTN
Connector Type	Braid
Material	Copper
UPC	781810157718
UPC 12 Digit	7818101577188

### Dimensions

Dimension - L Length Overall mm	2438 mm
Dimension - Length Overall inch	96.00 in
Length	96 in

### Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 10077022](#)  
[Specifications - BG96NTN](#)