



BG9D75NTN Flexible Copper Braid

By Burndy
Catalog # [BG9D75NTN](#)

Tin Plated Ferrules.



General

Connector Type	Braid
Material	Copper
UPC	781810509319
UPC 12 Digit	7818105093199

Dimensions

Dimension - L Length Overall mm	248 mm
Dimension - Length Overall inch	9.75 in
Length	9.75 in

Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

[3D Models - BG9D75NTN_MODEL-PDF](#)
[3D Models - BG9D75NTN_MODEL-IGES](#)
[3D Models - BG9D75NTN_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10077022](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-BG9D75NTN-SPEC-EN | REV 5/2024