

BIBD2/012FX, Double Sided Flex Rated Twelve Conductor Clear Insulated Mult-Tap Connector



By Burndy
Catalog # [BIBD2/012FX](#)

Aluminum UNITAP, Double Sided Entry, #14-2/0 Class B & C ,#14-#1 Class G,H,I,K, DLO, 12 PORT.

Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

General

Catalog Number	BIBD2/012FX
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	621945438750
UPC 12 Digit	6219454387500

Electrical Ratings

Voltage - Maximum 600 V

Conductor Related

Conductor Size 14-2/0 AWG
Conductor Type

- AL C Str-Size
- CU C Str-Size

Certifications And Compliance

Certification - CSA Approved Yes
Industry Standard(s) UL 486A-486B
Standards - Industry Standards UL 486A-486B
Met
Standards - RoHS Compliance CM
Status
UL Listed Yes

Logistics

Minimum Pack Quantity 5

Product Assets

[Catalogs - UNITAP™ Products](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50046931](#)
[Specifications - BURNDY_BIBD2012FX_Specsheet](#)
[Specifications - BIBD2/012FX](#)