

# BIBD2/012FXMT, Double Sided Mounted Flex Rated Twelve Conductor Clear Insulated Mult-Tap Connector



By Burndy  
Catalog # BIBD2/012FXMT

Aluminum UNITAP, Mountable Double Sided Entry, #14-2/0 Class B & C ,#14-#1 Class G,H,I,K, DLO, 12 PORT.

## Features

- Clear Plastisol covered AL6061-T6 aluminum body saves times and lowers installation costs and eliminates taping
- Clear plastisol allows visual confirmation that conductor is properly inserted
- Oxide inhibitor pre-installed inhibits moisture and contaminants from entering the contact area
- Range-taking capability reduces number of connectors necessary to carry in inventory
- Suitable for Code and Flex Conductor
- Color-coordinated conductor port caps display wire range and classes of conductor accepted
- Screw port caps show installation torque information for easy reference

## General

Catalog Number	BIBD2/012FXMT
Connector Type	Multi Tap
Insulation	Y
Material	Aluminum
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	621945439993
UPC 12 Digit	6219454399933

## Electrical Ratings

Voltage - Maximum 600 V

## Conductor Related

Conductor Size 14-2/0 AWG  
Conductor Type
 

- AL C Str-Size
- CU C Str-Size

## Certifications And Compliance

Certification - CSA Approved Yes  
Industry Standard(s) UL 486A-486B  
Standards - Industry Standards UL 486A-486B Met  
Standards - RoHS Compliance CM  
Status  
UL Listed Yes

## Logistics

Minimum Pack Quantity 5

## Product Assets

- [Catalogs - UNITAP™ Products](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50050187](#)
- [Specifications - BURNDY\\_BIBD2012FXMT\\_Specsheet](#)
- [Specifications - BIBD2/012FXMT](#)